

產品指南

這份指南說明配件網站上的資訊建構方式。這是為了讓您盡可能輕易獲得您找尋的資訊。

合作夥伴群

合作夥伴群是一個集合名稱，代表合併到一個區域的一些市場。AME=北美洲 EUR=歐洲 INT=國際其他 NOR=北歐國家

國家代碼

相關國家的國家代碼依據ISO 3166-1所述，例如SE代表瑞典、DE代表德國而US代表美國。

底盤編號

一些產品供應狀態必須依據底盤編號決定，例如車輛是否在車型年份中間修改過。VIN代碼（車輛識別編號）是製造編號，製造出來的每輛車都會有一個識別碼，也稱為底盤編號(Ch)。底盤編號的數字順序可能會依據車輛製造工廠而異。VIN代碼的第11個字元依據Volvo的（製造商的）清單，指出車輛是在哪間工廠製造。

1. 為車輛選取的設定檔會顯示在這裡。這是用於篩選資訊，以便只顯示符合選取設定檔的配件。
2. 搜尋框，可透過輸入全部或部分配件標題而搜尋不同配件。搜尋依據選取的設定檔而定。也可以透過勾選「Search all models」（搜尋所有車型）方框而搜尋所有車輛型號的不同配件。
3. 用於指名配件的標題。
4. 參照Volvo標準作業時間指南的操作號碼。這個號碼表明安裝配件需要多長時間。顧客自行安裝的配件不會列出操作號碼。
5. 適用於相關配件的配件零件編號以及任何條件，會顯示在這裡。
6. 產品前方的加號表示這是一項補充產品。需要此產品才能達成完整且正常運作的配件。
7. 可下載或以HTML或PDF格式開啟的裝配說明。
8. 產品的建議配件。
9. 參照Volvo的圖片資料庫Contentstore之照片編號。
10. 附註方框包含重要資訊，例如警告、注意事項或特定法律要求。
11. 提供補充資訊的註腳。
12. 日期代表產品頁面最後更新時間。

The screenshot shows the Volvo Accessories website interface. At the top, there are navigation menus for 'Cars' and 'Services', and the Volvo logo. A search bar is prominently displayed with the text 'Search Accessories' and a magnifying glass icon. Below the search bar, there are several filter buttons: 'Safety & Security', 'Comfort & Convenience', 'Tech & Sounds', 'Exterior Styling', 'Interior Styling', 'Wheels', 'Performance', and 'Pack & Load'. The 'Wheels' button is selected. The main content area shows a product listing for a '22" 20-Spoke Black Diamond Cut Alloy Wheel - 800147'. The product image is a large, detailed view of the wheel. To the left of the image, there is a list of specifications and options, including 'Op. No.: 77104', 'Part. No. 32207757', '+ Hub cap', 'Part. No. 31471435', 'Description Silver', '+ Application, speedometer, steering gear and tyre dimensions', 'Part. No. 32270049', 'Recommended accessories: Locking wheel bolts', and 'Technical data' such as 'Aluminum rims: 9 x 22"', 'Colour code: 019 (Black)', 'Accessory weight: 18.5 kg (41 lbs)', 'Recommended tyre size: 275/35 R22 104W XL VOL', 'Offset: 38.5 mm', and 'Photo: VCC13226'. There are also social media icons and an 'Add to wish list' button. The page is annotated with numbers 1 through 12, corresponding to the instructions on the left.